

TECHNICAL BULLETIN**INFORMATION ONLY**

For the Attention of : Installers

Date : 02-09-09

Product : Lift Interior Suspended Ceiling / Roof Lamp

Subject : Lamp Holder

Pages : 2

Originator : Stannah Lifts Ltd, Anton Mill, Andover, Hants SP10 2NX 01264 339090

Background

The original car lighting lamps with the 50mm bayonet P/N 500899 is no longer available and has been replaced with P/N 501683 with a 40mm bayonet which is now effective.

Therefore an additional plate with clip P/N PROT1046B is required to hold the lamps in place and to stop the lamp moving or rattling.

The additional plate with clip P/N PROT1046B are required on ten jobs which were manufactured before the new design change could be implemented the jobs are as follows:- LC290015, LR290168, LT290144, LC290075, LC280380, LC290140, LC290158, LT290121, LT290160 & LC280388.

Fitting

To fit the plate with clip P/N PROT1046B firstly drop the suspended ceiling to gain access to the lamps undo the fixing screws and remove the lamp holder angle bracket P/N 2000638 from the roof. Position the angle P/N 2000638 on top of the plate P/N PROT1046B refit in the same place using the fixing screws refit the lamps P/N 501683. All lamps and brackets are in a separate box within the stillage.

NOTE: the spring clip may need prising open to make the fitting easier.

